

Delta HEADER LATERAL Screens

DIRECTING THE FLOW WHERE IT NEEDS TO GO.

Header laterals by Delta Screens promote even distribution while also avoiding flow/pressure concentrations. Each header lateral consists of a series of screen laterals connected to a central header to provide uniform flow within a vessel containing treatment media. Header laterals can be used to either distribute inflow or collect flow, depending on their location within a vessel.

We build header laterals to your specifications for material (stainless steel options or alloys), wire and rod size, as well as open area to accommodate your media retention and flow rate requirements.

No matter the final design, you can count on a header lateral that will require minimal maintenance and provide exceptional durability.



For flow distribution and collection in either upflow or downflow systems.

www.deltascreens.com P.O. Box 842397 Houston, Texas 77284 main: 713-856-0300 fax: 713-856-0303